Day

Month

Year

## Semi-aqueous cleaning agent moisture meter Specification confirmation

	Date: /	/	/
Company name			
Person in charge			
Company address			
Telephone number			
End-user			
Operating conditions			
Cleaning agent name			
Manufacturer name			
Explosion-proof	□Necessary □Unnecessary		
Object be cleaned	□Oil □Flux □liquid crystal □Other (		)
Measuring range	% ~ %		
Dirt degree range	max %		
Cleaning agent temperat	ure °C		)
Measurement accuracy	□±1.0% □Other (		)
Cleaning method type	□Shower □Ultrasound □Vacuum □Other (		)
Installation location	□SubTank □WashingTank □Pipe □Other (		)
Wetted part material	□SUS-304 □Teflon (PTFE) □Other (		)
O-ring material	□Viton(Fluororubber) □EPDM □Silicon □Other (		)
Ambient temperature	${\mathbb C}$		
Operating hours/day	□24hours □Other (		)
Ambient pressure	□max0.3MPa □Other(		)
Alarm contact(Upper or I	ower limit)   Necessary   Unnecessary		
Purpose	□Monitoring □Control		
Air bubble amount	□large □Small		
Installation situation	□Outdoor □Indoor □Clean room		
Input power supply	□AC100V □Other(		)
C-TESTER_*	□Necessary □Unnecessary		
Remarks(Simple illustrat	ions etc.)		
- C TECTED :			
«C-TESTEK IS a device that chec	ks the normality of the moisture-meter in case of malfunction. C-TESTER canr	iot be so	טונ

%If you would like us to measure your sample, please let us know if the sample is toxic and how to dispose of the sample.

	技術	営業

<sup>\*\*</sup>C-TESTER is a device that checks the normality of the moisture-meter in case of malfunction. C-TESTER cannot be sold separately after the moisture meter is delivered, because C-TESTER is manufactured to fit each individual moisture meter. please note.